

HAND HYGIENE SOLUTIONS

PRODUCT	NAME	DESCRIPTION	PACK SIZE	PART #
General Use Hand Soaps	Clean & Smooth	Green Seal™ certified lotion hand soap provides rich, moisturizing lather to remove stubborn dirt while leaving hands fresh and soft.	6-750 mL	6100706
			4-1250 mL	6100707
	Foam Hand Soap	Green Seal™ certified gentle foaming hand soap that is ideal for public restrooms.	6-750 mL	6100708
			4-1250 mL	6100709
Antibacterial Hand Soap	Advanced Antibacterial Foam Hand Soap	Foam hand soap with a light floral scent that contains benzalkonium chloride. Effective against most common bacteria that may cause illness in food service environments.	6-750 mL	6101090
			4-1250 mL	6101088
	Advanced Antibacterial Clean & Smooth	High-quality lotion soap that is gentle on hands, with a benzalkonium chloride active ingredient for antimicrobial efficacy.	6-750 mL	6101421
			4-1250 mL	6101420
Hand Sanitizer	Instant Hand Sanitizer Gel	Formula is more than 99.5% effective helping to minimize the spread of contamination. It contains a unique ingredient for superior after-feel.	6-750 mL	6100722
			4-1200mL	6100723

NEXA DISPENSERS

PRODUCT	DESCRIPTION	BLACK	WHITE
Nexa Touch-Free Dispenser	Black Touch-Free Dispenser Nexa Classic - 92021192	Nexa Classic Touch-Free Dispenser (1250 mL) 9202-1192	9202-1193
		Nexa Compact Touch-Free Dispenser (750 mL) 9202-1190	9202-1191
Nexa Manual Dispenser	White Manual Dispenser Nexa Classic - 92023091	Nexa Classic Manual Dispenser (1250 mL) 9202-3091	9202-3093
		Nexa Compact Manual Dispenser (750 mL) 9202-3087	9202-3088



NEXA HAND SANITIZER STATION

Part # 9202-6037

One Nexa Hand Sanitizer Station with Two Front Panel Inserts



Nexa™ Hand Hygiene Program
Clean without a doubt.

Contact Your Ecolab Representative Today
Caribbean 876 926 0750

USE FOAM HAND HYGIENE SOLUTIONS FOR BETTER COST CONTROL AND A MORE SOPHISTICATED EXPERIENCE



- ▲ Foam provides better coverage than liquids
- ▲ Less product needed - use 0.7 - 1.0 mL foam hand soap compared to 1.0 - 1.4 mL liquid hand soap
- ▲ Foam rinses quickly and easily with less water usage, reducing your total costs

SAME DISPENSER CAN BE USED FOR FOAM, LIQUID OR GEL



Manual dispenser has bacteria-resistant coating on push bar to inhibit growth of bacteria, mold and mildew



Touch-free dispenser helps minimize spread of germs

DID YOU KNOW?

an estimated
80%
of all infections
are transmitted by
hands.¹

95%
of people don't
wash their hands
adequately.³

3
Days

is the amount of time
some germs can live
on moist surfaces.²

INCREASE EFFICIENCY AND REDUCE WASTE

- ✓ **Up to 99%** of product is dispensed from cartridge
- ✓ **Adjustable dosage** provides better control
- ✓ **Energy-saving dispenser** uses 44% less batteries than traditional dispensers
- ✓ **Locking system** prevents pilfering



¹ <http://www.cdc.gov/cdct/handtogether/>
² <http://www.flu.gov/planning-preparedness/hospital/influenzaguidance.html>
³ <http://msutoday.msu.edu/news/2013/eww-only-5-percent-wash-hands-correctly/>